



Powering Business Worldwide

pe.eaton.com

Type CHQ 3/4-inch Classified Replacement Breaker

CHQ215

UPC:782113010892

Dimensions:

- **Height:** 3 IN
- **Length:** 2.5 IN
- **Width:** 1.5 IN

Weight: .6 LB

Notes: Replacement for Square D Type QO Breakers. Requires two 3/4-inch (19.1 mm) spaces.

Warranties:

Specifications:

- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CHQ
- **Wire Size:** (1) #14-8, (2) #14-10 AWG Cu/Al
60°C or 75°C
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CHQ215](#)

Certifications:

- UL 489

Product compliance: No Data

