



Measurements:

<u>Height</u>	<u>Width</u>	<u>Extension</u>
6.00"	29.00"	2.21"
<u>BP Height</u>	<u>BP Width</u>	
4.25"	6.25"	
<u>Hanging Weight</u>		
5.06 lb		

Lamping:

Incandescent MB Incandescent	4,600 Rated Lumens
4.00 100W MB Incandescent	Color Temperature
400 total watt	2,500 Rated Life
Dimmable : Standard	

Shipping:

<u>Carton Weight</u>	<u>Carton Width</u>	<u>Carton Height</u>	<u>Carton Length</u>
6.82 lb	8.07"	8.86"	26.77"
<u>Master Pack Qty</u>	<u>UPC</u>	<u>UPS</u>	
1.0000	783209268913	Yes	

Finish:

Satin Nickel SN

Glass:

Marble MR

Material:

Steel

Certification:

Damp Location  
Location

Additional:

MB Incandescent (Not Included)  
Lighting Direction: Both