



Timer Controls: Plug-In Timers

P1121 | Outdoor Mechanical Plug-In Timer with Built-In Enclosure



P1121

OUTDOOR MECHANICAL PLUG-IN TIMER WITH BUILT-IN ENCLOSURE

These plug-in timers are grounded and utilize a flip-open enclosure rated for outdoor use. Great for providing timer function to pumps, landscaping or holiday lighting.



Features & Applications

Features

- 2 ON/2 OFF settings per day with removable trippers, more ON/OFF events with addition of extra trippers

Applications

- Pumps
- Water Fountains

- Minimum 30-min ON/OFF time
- Built into outdoor rated enclosure with clear or black flip cover
- Grounded standard or locking type style NEMA plug and receptacle
- Plugs directly into wall outlet
- Aerators
- Landscape/Holiday Lighting
- Engine Block Heaters

Specifications

Usage Environments	Input Voltages Display	Product Width (in)
Outdoor	120 VAC, 60Hz	3 5/8
Mechanism Type	Resistive	Product Width (mm)
Analog/Mechanical	15 A, 120 VAC, 60 Hz	92
Number of Plugs	Tungsten	Product Depth (in)
0	1800 W, 120 VAC, 60 Hz	3 1/4
Plug Configurations	Motor	Product Depth (mm)
5-15	1 HP, 120 VAC, 60 Hz	83
Color	Product Height (in)	Warranty
Black	5 5/8	1-year limited
Cover Color	Product Height (mm)	
Black	143	