


[On Line Catalog](#)


**BURNDY Catalog Number** YA272TC38  
**UPC Number** 7818100198566  
**Description** CUHYLUG 3/0AWG 2 HOLE 3/  
**Status** Active

**Web Use**  
 BURNDY Product Line

**Dimensional**

Tongue Angle	Straight
Length (in)	3.82
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.39
Barrel Type	Long
Thickness	0.12
B Length (in)	1.50
Pad Width (in)	0.90
E - in	1.00
Strip Length	1-9/16

**General**

Number of Holes	2
Product Description	Copper Compression lug, 2 Hole w/o Inspection Window, 3/0 AWG, 3/8" Stud, 1" stud hole spacing, Long Barrel, Tin Plated

**Conductor(s)**

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	3/0 AWG
DLO Size (Range)	N/A
Copper Stranded (Range)	3/0 AWG

**Physical**

Type of Plating	Tin - Electro Plated
Bolt Hole Size	3/8
Color Code	Orange
Plated (Yes or No)	Y
Index Number	14
Product Material	Copper

**Approvals / Certifications**

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B

**Documentation**

For further technical assistance, please contact us