

DATE: _____ TYPE: _____

NAME: _____

PROJECT: _____

Incandescent

P5265-31

Dome

One-light black cast aluminum dome spreadlight with white inner-lined shade for maximum light output. Clear acrylic enclosure under shade. Side mount allows the unit to be mounted towards the edge of a garden or walkway. 1/2 NPS threaded stem included.

- Black powder coat finish.
- White inner-lined shade.
- Wet location listed.

Category: Landscape

Finish: Black (powdercoat)

Construction: Aluminum construction
acrylic



Diameter: 9"
Height: 27-1/2"

MOUNTING	ELECTRICAL	LAMPING	ADDITIONAL INFORMATION
1/2 IN NPS thread mounted One 23" lengths of stem included	Pre-wired 24 in of wire supplied 120 V	Quantity: One 100w Medium Base Medium base porcelain socket	UL-CUL Wet location listed 1 year warranty