



**ALLIED
MOULDED
PRODUCTS, Inc.**

**419-636-4217
222 N. Union St.
Bryan, OH 43506**



Product Info

Brand: Control Series

UPC: 85339924012

UNSPSC: 39121324

Carton Quantity: 1

Carton Weight: 24 lbs

Country of Origin: United States of America

Color: Gray (RAL 7035)

Material: ULTRAGUARD® Fiberglass reinforced polyester - compression molded SMC box and Cover

Additional Materials: 316 stainless steel external hardware (hinges/latches/fasteners), 316 stainless steel mounting brackets, Plated carbon steel internal hardware, Brass inserts, Polyurethane (FIP) Formed-In-Place gasket system

AM24208RL

24"x20"x8" Control Series fiberglass wall mount enclosure assembly with raised hinged cover and stainless-steel snap latches

Availability:

In-Stock (Usually ships within 48 hours of receipt of order)

Enclosure Type: Wall Cabinets

Cover Type: Opaque

Closure Type: metal snap latch

Mounting Description: Stainless steel feet fastened to back side brass inserts

Box Features:

Installation Type:

Height: 24 in

Width: 20 in

Depth: 8 in

Usable Depth: 8.65 in

Volume: 4742 cu in

Features:

Non-corrosive, non-conductive, light weight with lower installation cost, easy to modify and longer life cycle compared to steel. Rigid design with back panel inserts plus stainless steel mounting brackets and a gasket system encased in a continuous channel on the cover.

Application:

Enclose and protect electrical and electronic controls, instruments or components for indoor and outdoor applications. Especially well suited for extreme temperature and corrosive environments.

Standards:

UL 508A, UL 50 and UL 50E Types 1, 2, 3, 3R, 4, 4X, 12 and 13; [File No. E120175](#)

CSA-C22.2 No. 14 and CSA C22.2 No. 94 Types 1, 2, 3, 3R, 4, 4X, 12 and 13; File No. 89590

Complies with:

1. EN / IEC 60204-1 and 60529 Type IP66
2. RoHS directive



WARNING - PROP 65
[Click here for more information!](#)