



# Steel City

## Recessed Service

**T&B Catalog Number:**

664-SC

**UPC Number:**

78599161882

**Status:**

Active

**Description:**

Two Gang Recessed Service Floor Box, 90 Cubic Inches, Length 10-1/4 Inches, Width 4-11/16 Inches, Depth 3-3/4 Inches, 3/4 Inch and 1 Inch Conduit Hubs, Cast Iron, Delivers Power, Communications and Data from Standard Conduit with No Exposed Service Fittings

### Features

	Hinged floor plate is steel reinforced for superior load bearing and provides easy access to devices
	Carpet covering eliminates unsightly service fittings and metal floor plates
	Power cords & low voltage cables run through retractable exit
	Power and communications/data can be disconnected quickly
	Accepts 2 plates, one duplex plate provided.
	Blank partitions available

### Application

	Multiple service floor box that deliver power, communications and data from standard conduit with no exposed service fittings.
--	--

### General

Material	Stamped Steel
Volume (cu.in.)	90
Number of Gangs	2
Conduit Knockouts-Sides	(4)-1 & 1 1/4 concentric & (4)-3/4
Conduit Knockouts-Bottom	None
Before Pour Adjustment (inches)	2 1/2
After Pour Adjustment (inches)	3/4
Wiring Device	Duplex and/or Data/Voice Plate
Box Material	Stamped Steel

### Dimension Information

Dimension A (inches)	3 3/4
Dimension B (inches)	4 11/16
Dimension C (inches)	10 1/4

### Specifications

3dmodel	Available on Website
Product Specification-DOC	Available on Website
Product Specification-PDF	Available on Website

### Accessories & Components

Covers & Carpet Plates-664 SC & 664 CI sf\_664scci\_accessories

### Competitor Cross Reference

Competitive Cross Reference Guide	Available on Website
-----------------------------------	----------------------

**Packaging**

T&B Inner Pack	1
Package in Units	4
T&B Sold in UOM	Each
T&B Weight Per UOM	352 lbs. per 100

**Application Support**

T&B Instruction Sheets	ta02125-tb2
Product Brochure - Brass & Aluminum	Available on Website
Floor Box Covers	
Floor Box Selection Guide	Available on Website
Product Brochure - MopTite Covers	Available on Website

**Notes**

*Note	When using the center side knockouts, catalog number 664-RP must be assembled to the box prior to installing the conduit.
**Note	When ordering a 664 Series box the cover must be ordered separately.

**Certifications**

RoHS Compliance	No
-----------------	----

**Certifications**

File Nbr:

E 2969

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com