

B2436 -- Flush Concrete Floor Box Series



B2436

Rectangular Metallic Floor Boxes, 1-G Deep Cast Iron, Brass Top

Product Specifications	
Product Application	 <p>Floor Boxes</p>
Product Type	 <p>Rectangular Metallic</p>
Box Material	Cast Iron
Box Capacity	Full Size
Trim Ring Color	Brass
Box Depth	Deep
Box Gangs	1
Box Adjustability	Fully
Minimum Depth of Pour	3.75" (95.3), 3.75"
Box Hubs/Knockouts	Standard
Material	Cast Iron
Dimension A	4.38" (111.2)
Dimension B	3.19" (81.0)
Dimension C	3.19" (81.0)
Before Pour Adjustability	1.25" (31.8)
After Pour Adjustability	.38" (9.5)
Total Cubic Inch Capacity (cm3)	33.00 (838.2)
Threaded Conduit Hubs	3/4" Four Way
Listings	UL Listed, CSA Certified
UPC Number	78358510030
Weight in LBs	4.75
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

