

## Rigid Non-Metallic Conduit Bodies & Covers

### T&B Catalog Number:



**UPC Number:**

E983H-CAR

**Status:**

03448113234

**Description:**

Active

Type T Conduit Body, Volume 32 Cubic Inches, Size 1-1/2 Inch, Length 8-21/32 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit, Pack of 4

### Features

Textured lids

Foam-in-place gasket

### Application

For use with Rigid Conduit

### General

Trade Size (inches)

1-1/2

Material

Non-Metallic

Volume (cu.in.)

32

Conduit Body Shape

T

### Dimension Information

C (inches)

1 3/32

H (inches)

2 5/16

L1 (inches)

8 21/32

L2 (inches)

6 13/32

L3 (inches)

4 21/64

Q (inches)

2 1/2

W (inches)

2 3/4

### Packaging

T&B Order Multiple

4

Package in Units

4

T&B Sold in UOM

Each

T&B Weight Per UOM

75 lbs. per 100

### Application Support

T&B Sales Drawings

wsd-ac04549

Rigid Non-metallic Conduit Bodies

Available on Website

Specifications & Applications

Available on Website

### Certifications



File Nbr:

E11461

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com