

ELECTRIC BASEBOARD - STEEL ELEMENT CONVECTION HEATERS



- Available in white or ivory with steel heating element and aluminum fins
- Painted 22ga. steel front with 20 ga. junction boxes located on each end of the heater - junction boxes contain quick connect cable clamps and 6" ground lead wires
- Over-temperature thermal limit extends entire length of heated area
- A full length wireway provided along the back of the heater
 - optional wireway covers are available
- Heater can be mounted to the wall by using the key hole knockouts every 4" at the back of the heater
- Optional In-Built thermostats field installed in the junction box
- HEIGHT - 6" DEPTH - 2 1/2"

UPC 686334	IVORY MODEL	UPC 686334	WHITE MODEL	WATTS	BTU's	VOLTS	AMPS	HEATER LENGTH (IN)	WT. (LBS.)	LIST
104302	E2903-024S	104999	E2903-024SW	375	1275	120	3.1	24	5	55
104319	F2903-024S	105002	F2903-024SW	375	1275	208	1.8			
104326	H2903-024S	105019	H2903-024SW	375 / 281	1275 / 955	240 / 208	1.6/1.4			
104333	G2903-024S	105026	G2903-024SW	375 / 281	1275 / 955	277 / 240	1.6/1.2			
104340	E2905-028S	105033	E2905-028SW	500	1706	120	4.2	28	6	57
104357	F2905-028S	105040	F2905-028SW	500	1706	208	2.4			
104364	H2905-028S	105057	H2905-028SW	500 / 375	1706 / 1275	240 / 208	2.1/1.8			
104371	G2905-028S	105064	G2905-028SW	500 / 375	1706 / 1275	277 / 240	1.8/1.6			
104388	E2906-036S	105071	E2906-036SW	600	2040	120	5.0	36	7	64
104395	F2906-036S	105088	F2906-036SW	600	2040	208	2.9			
104401	H2906-036S	105095	H2906-036SW	600 / 450	2040 / 1530	240 / 208	2.5/2.2			
104418	G2906-036S	105101	G2906-036SW	600 / 450	2040 / 1530	277 / 240	2.2/1.9			
104425	E2907-040S	105118	E2907-040SW	750	2550	120	6.3	40	8	66
104432	F2907-040S	105125	F2907-040SW	750	2550	208	3.6			
104449	H2907-040S	105132	H2907-040SW	750 / 563	2550 / 1914	240 / 208	3.1/2.7			
104456	G2907-040S	105149	G2907-040SW	750 / 563	2550 / 1914	277 / 240	2.7/2.6			
104463	E2910-048S	105156	E2910-048SW	1000	3413	120	8.3	48	10	80
104470	F2910-048S	105163	F2910-048SW	1000	3413	208	4.8			
104487	H2910-048S	105170	H2910-048SW	1000 / 750	3413 / 2550	240 / 208	4.2/3.6			
104494	G2910-048S	105187	G2910-048SW	1000 / 750	3413 / 2550	277 / 240	3.6/3.1			
104500	G2907-048S	105194	G2907-048SW	750	2550	277	3.4			
104517	E2912-060S	105200	E2912-060SW	1250	4250	120	10.4	60	12	99
103008	F2912-060S	105217	F2912-060SW	1250	4250	208	6.0			
103015	H2912-060S	105224	H2912-060SW	1250 / 938	4250 / 3189	240 / 208	5.2/4.5			
103022	G2912-060S	105231	G2912-060SW	1250 / 938	4250 / 3189	277 / 240	4.5/3.9			
103039	G2909-060S	105248	G2909-060SW	938	3189	277	3.4			
103046	E2915-072S	105255	E2915-072SW	1500	5100	120	12.5	72	14	113
103053	F2915-072S	105262	F2915-072SW	1500	5100	208	7.2			
103060	H2915-072S	105279	H2915-072SW	1500 / 1125	5100 / 3825	240 / 208	6.3/4.7			
103077	G2915-072S	105286	G2915-072SW	1500 / 1125	5100 / 3825	277 / 240	5.4/4.7			
103084	G2911-072S	105293	G2911-072SW	1125	3825	277	4.1			
103091	F2917-084S	105309	F2917-084SW	1750	5950	208	8.4	84	16	125
103107	H2917-084S	105316	H2917-084SW	1750 / 1313	5950 / 4464	240 / 208	7.3/6.3			
103114	G2917-084S	105323	G2917-084SW	1750 / 1313	5950 / 4464	277 / 240	6.3/5.5			
103121	G2913-084S	105330	G2913-084SW	1313	4464	277	4.7			
103138	F2920-096S	105347	F2920-096SW	2000	6826	208	9.6	96	18	138
103145	H2920-096S	105354	H2920-096SW	2000 / 1500	6826 / 5100	240 / 208	8.3/7.2			
103152	G2920-096S	105361	G2920-096SW	2000 / 1500	6826 / 5100	277 / 240	7.2/6.3			
103169	G2915-096S	105378	G2915-096SW	1500	5100	277	5.4			
103213	F2925-120S	105422	F2925-120SW	2500	8532	208	12.0	120	22	151
103220	H2925-120S	105439	H2925-120SW	2500 / 1875	8532 / 6375	240 / 208	10.4/9.0			
103237	G2925-120S	105446	G2925-120SW	2500 / 1875	8532 / 6375	277 / 240	9.0/7.8			
103244	G2918-120S	105453	G2918-120SW	1875	6375	277	6.8			