



Powering Business Worldwide

pe.eaton.com

Heavy Duty Safety Switch

DH365URK

UPC: 782113207230

Dimensions: 45.5 IN * 24.38 IN * 10.25 IN (L * W * H)

Notes: Suitable for service entrance use with a neutral or ground lug kit installed

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Single-Throw
- **Amperage Rating:** 400A
- **Enclosure:** NEMA 3R
- **Enclosure Material:** Painted galvanized steel
- **Fuse Configuration:** Non-fusible
- **Number Of Poles:** Three-pole
- **Number Of Wires:** Three-wire
- **Product Category:** Heavy Duty, Non-Fusible
- **Voltage Rating:** 600V
- **Max Hp Rating:** 125 at 240 Vac TD 3 Ph, 250 at 480 Vac TD 3 Ph, 350 at 600 Vac TD 3 Ph, 50 at 250 Vdc

Supporting documents:

- [Eatons Volume 2-Commercial Distribution](#)
- [Drawing Dataset](#)
- [Eaton Specification Sheet - DH365URK](#)

Certifications: No Data

Product compliance: No Data

