



Powering Business Worldwide

pe.eaton.com

Eaton's Crouse-Hinds series EV LED Luminaire

EVLEDC201

Dimensions:

- **Height:** 12.75 IN
- **Length:** 7.25 IN
- **Width:** 7.25 IN

Weight: 12 LB

Warranties: No Data

Specifications:

- **Area Classification:** Hazardous/Classified Locations
- **Amperage Rating:** 0.30A
- **Frequency Rating:** 50/60 Hz
- **Lumens:** 1670
- **Voltage Rating:** 100-277 Vac
- **Wattage:** 30W
- **Type:** Luminaire only
- **Color Temperature:** Cool white
- **Drive Type:** AC
- **Equivalent Luminaire:** 100-200W incandescent
- **Globe Material:** Heat and impact resistant glass
- **Guard:** With guard
- **Material:** Copper-free aluminum
- **Mounting Style:** No mounting module
- **Power Factor:** 0.98

Supporting documents:

- [EV LED Luminaires Catalog Page](#)

Certifications: No Data

Product compliance: No Data



