



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR2020BC100

UPC: 782114867044

Dimensions: 3.88 IN * 14.31 IN * 16.75 IN (L * W * H)

Notes: Listed for use as service entrance equipment and shipped with a neutral bonding strap preattached

Warranty: 10 year

Specifications:

- **Special Features:** No feed-thru lugs
- **Type:** Main circuit breaker
- **Amperage Rating:** 100A
- **Box Size:** C2
- **Bus Material:** Copper
- **Cover:** Cover included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Number Of Circuits:** 20
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Wire Size:** #4-1/0 AWG Cu/Al at 60°C or 75°C
- **Mounting:** Combination
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and Loadcenters](#)
- [Eaton Specification Sheet - BR2020BC100](#)



Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.