



61940-782: One Light Mini-Pendant



Collection: Windgate

One Light Mini-Pendant in Heirloom Bronze Finish with Alabaster Glass Shade

Includes three interconnecting 12" stems and one 6" stem

UPC #:785652028588

Finish: Heirloom Bronze (782)

Dimensions:

Diameter: 7 1/2"

Height: 6 1/2"

Overall Height: 51"

Wire: 96" (color/Brown)

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 1 - Medium A19 100w Max. 120v - Not included
- 1 - LED Medium A19 8w Max. 120v - Not included
- 1 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Sloped ceiling mounting hardware included
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

- 1 Body - Steel - Heirloom Bronze
- 1 6" Stem - Steel - Heirloom Bronze
- 3 12" Stem - Steel - Heirloom Bronze

Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990P61940-WDG)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Alabaster	1				4 7/8	7 7/16	1 5/8			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy	7/8			5		

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	61940-782	1	785652028588	10	7.5	13.75	0.597	3.8	125	Yes
NJ Pallet		120		48	40	77	85.556	456		No

NV Pallet		120		48	40	72.5	80.556	456		No
-----------	--	-----	--	----	----	------	--------	-----	--	----