



77950-782: Two Light Semi-Flush Convertible Pendant Dimensions:



Diameter: 13"

Height: 11"

Height Flush: 9 1/2"

Overall Height: 48 3/4"

Wire: 96" (color/Brown)

Chain: 36"

Mounting Proc.: Center Lock-Up

Connection: Mounted To Box

Bulbs:

- 2 - Medium A19 100w Max. 120v - Not included
- 2 - LED Medium A19 8w Max. 120v - Not included
- 2 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Fixture is dual mount and may be installed semi-flush or as a pendant.
- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Collection: Windgate

Two Light Semi-Flush Convertible in Heirloom Bronze Finish with Alabaster Glass

UPC #:785652157004

Finish: Heirloom Bronze (782)

Material List:

- 1 Body - Steel - Heirloom Bronze
- 1 Chain - Steel - Heirloom Bronze

Safety Listing:

- Safety Listed for Dry Locations
- Safety Listed for Dry Locations

Instruction Sheets:

Bilingual (English - French) (HC-1890FS)

Shade / Glass / Diffuser Details:

| Part | Material | Finish | Quantity | Item Number | Length | Width | Height | Diameter | Fitter Diameter | Shade Top Length | Shade Top Width | Shade Top Diameter |
|-------|----------|-----------|----------|-------------|--------|-------|--------|----------|-----------------|------------------|-----------------|--------------------|
| Shade | Glass | Alabaster | 1 | | | | 3 5/16 | 9 29/32 | 15/16 | | | |

Backplate / Canopy Details:

| Type | Height / Length | Width | Depth | Diameter | Outlet Box Up | Outlet Box Down |
|--------|-----------------|-------|-------|----------|---------------|-----------------|
| Canopy | | 7/8 | | 5 | | |

Replacement Bulb Data:

| Product # | | | Type | Base | Watts | Watts Consumed | Volts | Hours | Lumens | Temp (°K) | CRI |
|-----------|---------|--|------|-------------|-------|----------------|-------|-------|--------|-----------|-----|
| 97308S | Frosted | | A19 | E-26 Medium | 8 | 8 | 120v | 50000 | 450 | 3000 | 85 |
| 97408S | Frosted | | A19 | E-26 Medium | 8 | 8 | 120v | 50000 | 450 | 2700 | 85 |
| 97309S | Frosted | | A19 | E-26 Medium | 13.5 | 13.5 | 120v | 50000 | 800 | 3000 | 85 |
| 97409S | Frosted | | A19 | E-26 Medium | 13.5 | 13.5 | 120v | 50000 | 800 | 2700 | 85 |

Shipping Information:

| Package Type | Product # | Quantity | UPC | Length | Width | Height | Cube | Weight | Fr. Class | UPS Ship |
|--------------|-----------|----------|--------------|--------|-------|--------|--------|--------|-----------|----------|
| Individual | 77950-782 | 1 | 785652157004 | 19.25 | 14 | 6 | 0.936 | 5.5 | 150 | Yes |
| NJ Pallet | | 77 | | 48 | 40 | 71.5 | 79.444 | 423.5 | | No |
| NV Pallet | | 77 | | 48 | 40 | 71.5 | 79.444 | 423.5 | | No |