



35940-782: Five Light Chandelier



Collection: Windgate

Five Light Chandelier in Heirloom Bronze Finish with Alabaster Glass Shades

UPC #:785652020322

Finish: Heirloom Bronze (782)

Dimensions:

Diameter: 20 1/2" **Overall Height:** 54 1/2"
Height: 16 3/4" **Wire:** 72" (color/Brown)
Chain: 36"
Mounting Proc.: Center Lock-Up
Connection: Mounted To Box

Bulbs:

5 - Medium A19 100w Max. 120v - Not included
 5 - LED Medium A19 8w Max. 120v - Not included
 5 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.
- Supplied with wire pre-laced through chain

Material List:

1 Body - Steel - Heirloom Bronze
 1 Chain - Steel - Heirloom Bronze

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

Bilingual (English - French) (HC-1699FB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Alabaster	5				4 3/8	5 7/16	1 5/8			

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Canopy			7/8	5		

Replacement Bulb Data:

Product #		Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted	A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted	A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	35940-782	1	785652020322	20	10	17.75	2.054	10.9	150	Yes
NJ Pallet		40		48	40	75	83.333	436		No

NV Pallet		40		48	40	75	83.333	436		No
-----------	--	----	--	----	----	----	--------	-----	--	----