

FM271BS: 1 - Light Indoor Flush Mount

Dimensions:

Diameter: 10"

Height: 4"

Weight: 4.6 lbs.

Bulbs:

1 - Medium A19 75w Max. 120v - Not included

Features:

•

Material List:

1 Body - Steel - Brushed Steel

Safety Listing:

Safety Listed for Dry Locations

Safety Listed for Dry Locations

Instruction Sheets:

English (FM271)



Collection: Barrington

UPC #: 014817330809

Finish: Brushed Steel (BS)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Etched Glass	Opal Etched	1				2 1/8	8 1/4				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Mounting Plate	1	4				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Frt. Class	UPS Ship
Individual	FM271BS	1	014817330809	16.5	13.5	6.75	0.87	5.555	125	Yes

Master Pack	FM271BS	2	10014817330806	16.5	13.5	13.5	1.74	11.11	125	Yes
NJ Pallet		80		48	40	71.5	79.444	499.95		No
NV Pallet		80		48	40	71.5	79.444	499.95		No