



Catalog No. TGN3322

Description: 60A 3P GD N1 240V NONFUSE SW

UPC No 783164008807

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > General Duty

- Designed for residential and light commercial applications where duty is not severe.
- Listed to UL standard 98 enclosed and dead front switches.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type GD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism (30-200 amp).
- 60/75°C conductor rating.

Descriptors

Category	General Duty
----------	--------------

Specifications

Amperage	60 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Wire Range (Cu/Al)	12-2
240 Vac, NEC Std, 1-ph	10
240 Vac, NEC Std, 3-ph	15
250 Vdc	10
GSA Compliance	Yes

Classifications

CSA Certified	Yes
---------------	-----

Dimensions

Height	13.8
Depth	4
Width	8.4
Weight	10

Publications

Title	Publication No.	Publication Type
General Duty Safety Switches: 30-600 Amp, 240 Vac	DEE-576	Brochures
1 page. For residential and light commercial applications.		
60A - Safety Switches	10103091-SH104	Drawings-Outline and Dimensional
1 page outline drawing in .pdf format.		

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.