



## Catalog No. TGN3323

**Description: 100A 3P GD N1 240V NONFUSE SW**

**UPC No 783164008821**

**Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > General Duty**

- Designed for residential and light commercial applications where duty is not severe.
- Listed to UL standard 98 enclosed and dead front switches.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type GD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism (30-200 amp).
- 60/75°C conductor rating.

### Descriptors

Category	General Duty
----------	--------------

### Specifications

Amperage	100 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Wire Range (Cu/Al)	10-1/0
240 Vac, NEC Std, 1-ph	15
240 Vac, NEC Std, 3-ph	30
250 Vdc	20
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
---------------	-----

### Dimensions

Height	21.3
Depth	4.9
Width	9.4
Weight	16

## Publications

Title	Publication No.	Publication Type
<a href="#">200A - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH108	Drawings-Outline and Dimensional
<a href="#">General Duty Safety Switches: 30-600 Amp, 240 Vac</a> 1 page. For residential and light commercial applications.	DEE-576	Brochures

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.