



Catalog No. TGN3324

Description: 200A 3P GD N1 240V NONFUSE SW

UPC No 783164008845

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > General Duty

- Designed for residential and light commercial applications where duty is not severe.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type GD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism (30-200 amp).
- 60/75°C conductor rating.

Descriptors

Category	General Duty
----------	--------------

Specifications

Amperage	200 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 1 (Indoor)
Wire Range (Cu/Al)	2-250
240 Vac, NEC Std, 1-ph	15
240 Vac, NEC Std, 3-ph	50
GSA Compliance	Yes

Classifications

CSA Certified	Yes
---------------	-----

Dimensions

Height	29.1
Depth	5.2
Width	13.4
Weight	30

Publications

Title	Publication No.	Publication Type
200A - Safety Switches 1 page outline drawing in .pdf format.	10103091-SH108	Drawings-Outline and Dimensional
General Duty Safety Switches: 30-600 Amp, 240 Vac 1 page. For residential and light commercial applications.	DEE-576	Brochures

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.