



GE
Lighting

69163 - 38PAR20H/FL25

38PAR20H/FL25

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Skirt
Base Type	Screw-In
Bulb Material	Sodalime glass
Filament	CC-8
Rated Life Hours-nominal	1500 h
Primary Application	Indoor Floodlight
Product Technology	Halogen
Base	E26/50x39
Bulb Shape	PAR20

PHOTOMETRIC CHARACTERISTICS

Beam Spread	25 deg
Center Beam Candle Pwr Candela	1450 cd
Nominal Initial Lumen per Watt	13
Initial Lumens-nominal	490 lm
Color Rendering Index-CRI	100

PRODUCT INFORMATION

Product Code	69163
Description	38PAR20H/FL25
Alternative Unit Of Measure	EACH
Standard Package Quantity	6
Ean UPC	043168691635
Standard Package GTIN	00043168691635
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	6
Sales Unit	Each
UCC	043168691635
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168691635
Standard Package GTIN	10043168691632
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168691635

DIMENSIONS

Diameter	2.5 in
----------	--------

ELECTRICAL CHARACTERISTICS

Burn Position	Universal
Input Voltage [nom]	120 V
Rated power (Watts)	38 W