



GE  
Lighting

68052 - F96T12/CW/C/WM

F96T12/CW/C/WM

Product Photo



#### GENERAL CHARACTERISTICS

Base Description	Single Pin
Base Type	Pin/Plug-In
Mercury Content	15 mg
Mercury-Picogram per mean lm hr	431
Starting Temp (MIN) C-degrees	15 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	12000 h
Primary Application	Energy Saving
Product Technology	Linear Fluorescent
Base	Fa8
Bulb Shape	T12

#### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2900 lm
Nominal Initial Lumen per Watt	60
Initial Lumens-nominal	3600 lm
Color Rendering Index-CRI	90
Color Temperature	4100 K

#### PRODUCT INFORMATION

Product Code	68052
Description	F96T12/CW/C/WM
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168680523
Standard Package GTIN	10043168680520
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168680523

#### DIMENSIONS

Diameter	1.5 in
Nominal Length	96.0 in

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	60 W
---------------------	------