



GE
Lighting

66649 - F34/CW/C/WM/ECO-LFL - 30PK WITH UPC STICKERS ON L
F34/CW/C/WM/ECO

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	5 mg
Mercury-Picogram per mean lm hr	222.2
Starting Temp (MIN) C-degrees	15 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	15000 h
Primary Application	Energy Saving
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T12

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1500 lm
Nominal Initial Lumen per Watt	53
Initial Lumens-nominal	1800 lm
Color Rendering Index-CRI	87
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	66649
Description	F34/CW/C/WM/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168666497
Standard Package GTIN	10043168666494
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168666497
Alternative Unit Of Measure	EACH
Standard Package Quantity	30
Ean UPC	043168666497
Standard Package GTIN	00043168666497
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	30
Sales Unit	Each
UCC	043168666497

DIMENSIONS

Diameter	1.5 in
Nominal Length	48.0 in

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	34 W
---------------------	------