

FM251GBZ: 2 - Light Indoor Flush Mount



Dimensions:

Diameter: 13" **Wire:** 8"
Height: 5 1/2" **Connection:** Mounted To Box
Weight: 3.34 lbs.

Bulbs:

2 - Medium A19 60w Max. 120v - Not included

Features:

- CFL Convertible. For commercial quotes, call 847.410.4602
-

Material List:

1 Body - Steel - Grecian Bronze

Safety Listing:

Safety Listed for Dry Locations
 Safety Listed for Dry Locations

Instruction Sheets:

English (2011B)

Collection: Vista

UPC #: 014817290059

Finish: Grecian Bronze (GBZ)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Cream Snow	1				3 1/4	10 1/2				

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Mounting Plate	1	4				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	FM251GBZ	1	014817290059	15	15	7.25	0.944	6.233	125	Yes

Master Pack	FM251GBZ	6	10014817290056	30.75	15.75	22.5	6.306	37.4	125	Yes
NJ Pallet		54		48	40	71.5	79.444	336.6		No
NV Pallet		54		48	40	71.5	79.444	336.6		No