

PLENUM CONTROL CABLE

Shielded Conductors
OMNIPLLEN



CONSTRUCTION	
Construction	- Stranded Bare copper
Insulation	- OMNIPLLEN
Jacket	- OMNIPLLEN

Applications:

- Power limited control circuits
- Wiring of the following systems:
 - -Intercom
 - -Security
 - -Audio
- Suggested Voltage Rating: 300 Volts

Standards:

- NEC Article 725-CL3P, CMP, MPP

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
G112202	22	2	.006"	.010"	.108"	11
G112203	22	3	.006"	.010"	.114"	16.5
G112204	22	4	.006"	.010"	.125"	17
G112206	22	6	.006"	.010"	.150"	23
G112208	22	8	.006"	.010"	.173"	30
G112210	22	10	.006"	.010"	.192"	35
G112212	22	12	.006"	.010"	.198"	41
G112002	20	2	.006"	.010"	.124"	16.2
G112003	20	3	.006"	.010"	.131"	21
G112004	20	4	.006"	.010"	.144"	26

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

COLOR CODE CHART	
Cond. #	Color
1	Black
2	Red
3	White
4	Green
5	Brown
6	Blue
7	Orange
8	Yellow
9	Purple
10	Gray
11	Pink
12	Tan