



S4641

40T4/G9/CL
40 watt; Halogen; T4; Clear; 2000 Average rated Hours; 500 Lumens; Double Loop base; 120 volts

Features

- Bright, Crisp light
- UV-Filter halogen capsule
- Uniform light output



S4641

Item Number		UPC		Watts	Voltage	Lamp Shape	Base	ANSI Base	Lamp Code
S4641		045923046414		40	120	T4	Double Loop	G9	40T4/G9/CL
Finish	MOL In Inches	MOD In Inches	Filament	Initial Lumens	Kelvin Temp	Color	Average Rated Hours		
Clear	1-9/16"	0.50"	CC-2V	500	2900	Warm White	2000		
Pack		Package Type		Dimmable/Non-Dimmable			RoHS Compliant		
960/48		Box		Dimmable			Yes		



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

