



Representative Image

## Catalog No. TH3366R

Description: 600A 3P HD N3R 600V FUSIBLE

UPC No 783164009187

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	600 AC
Amperage	600 A
Poles	3
Wires	3
Fusing	Fusible
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	(2) 4-500
240 Vac, NEC Std, 3-ph	75.0 hp
240 Vac, Time Delay, 3-ph	200.0 hp
480 Vac, NEC Std, 3-ph	150.0 hp
480 Vac, Time Delay, 3-ph	400.0 hp
600 Vac, NEC Std, 3-ph	200.0 hp
600 Vac, Time Delay, 3-ph	500.0 hp
250 Vdc	50.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	53.5 in
Depth	8.5 in
Width	23.0 in

**Dimensions**

Weight

136.0 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">Safety Switch HD Outline Drawing</a> 600A , NEMA 3R Enclosure	10103091SH140	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.