



Representative Image

## Catalog No. TH4321R

Description: 30A 3P HD N3R 240V FUSIBLE SW

UPC No 783164009200

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

### Descriptors

Category	Heavy Duty
GO Schedule	S1

### Specifications

Voltage	240 AC
Amperage	30 A
Poles	3
Wires	4
Fusing	Fusible
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	14-8 CU;12-8 AL
240 Vac, NEC Std, 1-ph	1.5 hp
240 Vac, NEC Std, 3-ph	3.0 hp
240 Vac, Time Delay, 1-ph	3.0 hp
240 Vac, Time Delay, 3-ph	7.5 hp
250 Vdc	5.0 hp
GSA Compliance	Yes

### Classifications

CSA Certified	Yes
UL Listed	Yes

### Dimensions

Height	10.5 in
Depth	3.1 in
Width	6.2 in
Weight	7.0 lb

## Publications

Title	Publication No.	Publication Type
<a href="#">60A - Safety Switches</a> 1 page outline drawing in .pdf format.	10103091-SH101	Drawings-Outline and Dimensional

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.