

TF1400SVB
Tiffany Flush Mount
Vintage Bronze
West End

Q U O I Z E L.®



DIMENSIONS

Dimensions: 17" W x 6" H x 17" D
Backplate Dimensions:
Canopy Dimensions: 7.00"W x 7.00"D
Weight: 4.10 lbs
Dimensional Weight: 17.00 lbs.

DETAILS

Material: STEEL
Glass/Shade Description: Tiffany Glass
Shade - Tiffany Glass

LAMPING

Light Source: Incandescent
Bulb Included: No
Bulb Type: Medium Base
Bulb Quantity: 2
Watts per Bulb: 75

ELECTRICAL

Dimmable: No
Voltage: 120v
Wire Length: 0.5'

INSTALLATION

Location Rating: Damp
Sloped Ceiling Compatible: Yes

We reserve the right to revise the design of components of any product due to parts availability or change in our Listed Mark standards without assuming any obligation or liability to modify any products previously manufactured and without notice. This literature depicts a product DESIGN that is the SOLE and EXCLUSIVE PROPERTY of Quoizel Lighting Inc. Compliance with U.S. COPYRIGHT and PATENT requirements, notidication is hereby presented in this form that this literature, or this product depicts, is NOT to be copied, altered or used in any manner without the express written consent of, or contray to the best interests of Qouizel Inc. 03/31/2013