

PLENUM CONTROL CABLE

Nonshielded Conductors
OMNIPLLEN



CONSTRUCTION	
Conductor	- Stranded Bare copper
Insulation	- OMNIPLLEN
Shield	- None
Jacket	- OMNIPLLEN

Applications:

- Power limited control circuits
- Wiring of the following systems:
 - -Intercom
 - -Security
 - -Audio
- Suggested Voltage Rating: 300 Volts

Standards:

- NEC Article 725-CL3P, CMP, MPP

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
G121802	18	2	.008"	.015"	.156"	16
G121803	18	3	.008"	.015"	.166"	23
G121804	18	4	.008"	.015"	.187"	30
G121805	18	5	.008"	.015"	.200"	36
G121806	18	6	.008"	.015"	.216"	43
G121808	18	8	.008"	.015"	.235"	58.2
G121810	18	10	.008"	.015"	.268"	70.6
G121812	18	12	.008"	.015"	.278"	83.2
G121602	16	2	.008"	.015"	.174"	21
G121603	16	3	.008"	.015"	.185"	29
G121604	16	4	.008"	.015"	.205"	38

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.

COLOR CODE CHART	
Cond. #	Color
1	Black
2	Red
3	White
4	Green
5	Brown
6	Blue
7	Orange
8	Yellow
9	Purple
10	Gray
11	Pink
12	Tan