3 Light Semi Flush Ceiling Light - Brushed Nickel

3627NI (Brushed Nickel)

Project Name:	
Location:	
Туре:	
Qty:	
Comments:	



Ordering Information

ĺ	Product ID	3627NI
	Finish	Brushed Nickel
-	Available Finishes	NI, OZ

Dimensions

Base Backplate	5.7 DIA
Weight	5.10 LBS

Specifications

Material	Steel
Glass Description	White Etched

Electrical

Voltage 120V

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	3
Max or Nominal Watt	100W
Socket Wire	150
Socket Type	Medium
Lamp Type	A19

Dimensions

Height	7.75"
Width	15.50"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	9-13W		