

Item #: 8272-A357-L	UPC Code: 747396087160
Product Family Name: Wickford Bay™	Finish: Iron Oxide
Category: Wall Mount	Category Type: Wall Bracket
Certification 3187291	
Patents	
Notes:	



Image File Name:
8272-A357-L--
1377129264.jpg



MEASUREMENTS

Width: 9	Length: 19.5	Height: 9.25	Extension: 9.25
Height Adjustable: No	Min Overall Height:	Max Overall Height:	Slope: No
Wire Length: 7	Chain Length:	Safety Cable Included: No	Net Weight: 4.48
Canopy Width: 4.75	Canopy Height: 7.75	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top: 10.00	Center to Bottom: 10.00

SHADE / GLASS

Description:	Material: Glass
Part No.: G8272	Quantity: 6
Width:	Height:
	Length:

LAMPING

No. of Bulbs: 1	Light Type: L-Ac10-Module			
Max Bulb Wattage: 10	Socket: Led			
Dimmable: No	Ballast:	Rated Life Hours: 30000	Photocell included:	Lamps included: Yes
LED Included: Yes	Color Temp.: 2700	CRI: 78	Initial Lumens: 450.000	Delivered Lumens: 231.000



SHIPPING

Carton Width: 11.630	Carton Height: 16.130	Carton Length: 11.630	
Carton Weight: 6.578	Carton Cubit Feet: 1.263	Small Package Shippable: Yes	
Master Pack Width:	Master Pack Height:	Master Pack Length:	
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:	Master Pack: 1

LED

LED

Yes



Wet Location

Yes



ETL Intertek

Yes