

Item #: **8276-A357-L**
Product Family Name: **Wickford Bay™**
Category: **Post Mount Lantern**
Certification: **3187291**
Patents

UPC Code: **747396087184**
Finish: **Iron Oxide**
Category Type: **Post Light**

Notes:



Image File Name:
8276-A357-L--
1377129264.jpg



MEASUREMENTS

Width:	Length:	Height:	Extension:
9.75	11.25	18	
Height Adjustable:	Min Overall Height:	Max Overall Height:	Slope:
No			No
Wire Length:	Chain Length:	Safety Cable Included:	Net Weight
7		No	6.28
Canopy Width:	Canopy Height:	Canopy Length:	
Backplate Width:	Backplate Height:	Center to Top:	Center to Bottom:

SHADE / GLASS

Description:	Material:
	Glass
Part No.:	Quantity:
G8276	6
Width:	Height:
	Length:

LAMPING

No. of Bulbs:	Light Type:
1	L-Ac10-Module
Max Bulb Wattage:	Socket:
10	Led
Dimmable:	Ballast:
No	
LED Included:	Color Temp.:
Yes	2700
	CRI:
	78
	Rated Life Hours:
	30000
	Photocell Included:
	Yes
	Lamps Included:
	Yes
	Initial Lumens:
	450.000
	Delivered Lumens:
	197.000



SHIPPING

Carton Width:	Carton Height:	Carton Length:
12.630	20.630	13.750
Carton Weight:	Carton Cubic Feet:	Small Package Shippable:
8.866	2.073	Yes
Master Pack Width:	Master Pack Height:	Master Pack Length:
Master Pack Weight:	Master Cubic Feet:	Multi-Pack:
		Master Pack:
		1

LED



Wet Location



ETL Intertek

LED

Yes

Yes

Yes