



Powering Business Worldwide

pe.eaton.com

Series C, F-frame Molded Case Circuit Breaker

EHD1015

UPC: 786679317310

Dimensions: 3.38 IN * 1.38 IN * 6 IN (L * W * H)

Notes: No Data

Warranty: Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Frame Size:** F-frame
- **Maximum Voltage:** 14 kAIC at 480V
- **Series:** Series C
- **Trip Type:** Thermal magnetic
- **Amperage Rating:** 15A
- **Number Of Poles:** Single-pole

Supporting documents:

- [MOEM MCCB Product Selection Guide Brochure](#)
- [Eatons Volume 4-Circuit Protection Catalog](#)
- [F-frame Molded Case Circuit Breaker Drawing Drawing](#)
- [Time Current Curves for Series C® F-Frame Circuit Breakers Drawing](#)
- [EHD1 3D Inventor Drawing](#)
- [EHD1 2D Drawing Xchange Drawing](#)
- [EHD1 2D PDF Drawing](#)
- [EHD1 3D Model Xchange Drawing](#)
- [Installation Instructions for EHD, EDB, EDS, ED, EDH, EDC, FDB, FD, HFD, FDC, HFDDC Circuit Breakers and Molded Case Switches Inst Leaflet](#)
- [Counterfeit and Gray Market Awareness Guide](#)



Product Aid

- [F-Frame 310+ Molded-case circuit breakers 15-225A Specification](#)
- [Types EHD and FDB 10 Amperes AB DE-ION Circuit Breakers Time Curr Curve](#)

Certifications:

- UL Listed

Product compliance: No Data