



Catalog No. THN3364R

Description: 200A 3P HD N3R 600V NONFUSE SW

UPC No 783164011357

Products > Switches & Disconnects > Disconnect & Safety Switches > Safety Switches > Heavy Duty

- Designed for commercial and industrial applications where safety, high performance and continuity of service are essential.
- Listed to UL standard 98 enclosed and dead front switches.
- Suitable for use as service equipment when installed in accordance with the National Electrical Code.
- Certified to CSA standard 22.2 no. 4-04 enclosed and dead front switches.
- Meets or exceeds NEMA KS1 standard for enclosed switches - type HD.
- Fusible and non-fusible switches available (consult BuyLog for interrupt ratings).
- Quick-make, quick-break mechanism.
- 60/75°C conductor rating.
- Full cover interlocks.

Descriptors

Category	Heavy Duty
GO Schedule	S1

Specifications

Voltage	600 AC
Amperage	200 A
Poles	3
Wires	3
Fusing	No Fuse
Enclosure	NEMA 3R (Outdoor)
Options	None
Wire Range (Cu/Al)	2-250
240 Vac, NEC Std, 1-ph	30.0 hp
240 Vac, NEC Std, 3-ph	60.0 hp
480 Vac, NEC Std, 1-ph	50.0 hp
480 Vac, NEC Std, 3-ph	125.0 hp
600 Vac, NEC Std, 1-ph	50.0 hp
600 Vac, NEC Std, 3-ph	150.0 hp
250 Vdc	40.0 hp
GSA Compliance	Yes

Classifications

CSA Certified	Yes
UL Listed	Yes

Dimensions

Height	31.7 in
Depth	5.4 in
Width	13.4 in

Dimensions

Weight

33.0 lb

Publications

Title	Publication No.	Publication Type
Safety Switch HD Outline Drawing 200A	10103091SH182	Drawings-Outline and Dimensional

Additional Documentation: Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.