

Wedgeport Collection

Wedgeport 1 Light Mini Pendant in Brushed Nickel

3584NI (Brushed Nickel)



Dimensions

Height	7.00"
Overall Height	50.00"
Width	6.50"

Alternate Lamps

Lamp Included	Bulb Listing	Light Source	Max Wattage/Range	Bulb Product ID	Dimming
No	Hybrid	CFL	18-25W		

Project Name: _____
Location: _____
Type: _____
Qty: _____
Comments: _____

Ordering Information

Product ID	3584NI
Finish	Brushed Nickel
Available Finishes	NI, OZ, NI, OZ
Collection	Wedgeport Collection

Dimensions

Base Backplate	5.25 DIA
Chain/Stem Length	36.00"
Weight	2.00 LBS

Specifications

Material	Steel
Glass Description	Satin Etched

Electrical

Voltage	120V
Lead Wire Length	67.00"

Qualifications

Safety Rated	Dry
Warranty	www.kichler.com/warranty

Primary Lamping

Light Source	Incandescent
Lamp Included	Not Included
Number of Lights/LEDs	1
Max or Nominal Watt	100W
Socket Wire	105
Socket Type	Medium
Lamp Type	A19

Notes:

- 1) Information provided is subject to change without notice. All values are design or typical values when measured under laboratory conditions.
- 2) Incandescent Equivalent: The incandescent equivalent as presented is an approximate number and is for reference only.