



GE
Lighting

97618 - GE Ecolux® Blax® T4 - Facilities. Retail Display. Hospitality.

Office. Restaurant. Warehouse

F26TBX/827/4P/ECO

Product Photo



GENERAL CHARACTERISTICS

Base Type	Pin/Plug-In
Mercury Content	3 mg
Rated Life Hours-nominal	17000 h
Starting Temp (MIN) C-degrees	0 °C
Mercury-Picogram per mean lm hr	115.3
Primary Application	Facilities Retail Display Hospitality Office Restaurant Warehouse
Product Technology	Compact Fluorescent
Base	GX24q-3
Bulb Shape	T4

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1530 lm
Nominal Initial Lumen per Watt	69
Initial Lumens-nominal	1800 lm
Color Rendering Index-CRI	82
Color Temperature	2700 K

PRODUCT INFORMATION

Product Code	97618
Description	F26TBX/827/4P/ECO
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168976183
Standard Package GTIN	10043168976180
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168976183

DIMENSIONS

Nominal Length	5.2 in
Bulb Max Overall Length-MOL	5.2 in

ELECTRICAL CHARACTERISTICS

Equivalent Incandescent Watts	100 W
Rated power (Watts)	26 W

CAUTIONS & WARNINGS

Caution

Lamp may shatter and cause injury if broken

Remove and install by grasping only plastic portion of the lamp.