



SL12050TI-SS - 2" Directional, Round, Stainless

Product Features:

- 120V 50W max.
- Shallow 4 1/4" depth housing
- 10 year Rust Free warranty







Product Specifications:

Housing

- Powder coated 316L stainless steel construction.
- No Insulation Contact (Non-IC) rated.
- Air Tight as per ASTM E283 Standard.
- Approved for use in dry and damp locations.
- Approved for feed-through wiring.
- 4 1/4" housing depth.

Trim

- Round. Directional. Single gimbal 20° tilt.
- Powder Coated. Brushed finish is sealed.
- Finishes available: Brushed Steel (BS), White (WH).
- Lamp secured with wire retaining clip.

Warranty

- Ten year Rust Free warranty.
- Two year warranty against manufacturer defects in material or workmanship. Please refer to our Terms of Sale for full warranty terms and conditions.

Mounting

- Installs into 3/8" 1 1/4" ceiling thickness.
- Installs into 3" diameter hole.
- New Construction Mounting Plate (NCMP 3000) available. Comes with hanger bars.
- **WARNING:** Cannot be directly covered in polycell spray-in foam insulation.

Lamp

- 120V 50W max. GU10 based lamp.
- Reccomended lamp:120V 9W max. Soraa LED lamp.
- Halogen alternative: 120V 50W max. aluminum backed lamp.









SL12050TI-SS - 2" Directional, Round, Stainless

Product Dimensions:






Accessories:

NCMP 3000 - New Construction Mounting Plate Steel construction. 3" ø hole. Comes with hanger bars.



Ordering Code:







SL12050TI-SS - 2" Directional, Round, Stainless

Reccomended Soraa LEDs:

Soraa Vivid 95 CRI*:

Model	CCT (K)	Beam (°)	Power (W)	Lumens (Im)	CBCP
SM16GA-09-25D-927-03	2700K	25°	9W	465	2570
SM16GA-09-36D-927-03	2700K	36°	9W	465	1210
SM16GA-09-60D-927-03	2700K	60°	9W	465	470
SM16GA-09-25D-930-03	3000K	25°	9W	490	2700
SM16GA-09-36D-930-03	3000K	36°	9W	490	1280
SM16GA-09-60D-930-03	3000K	60°	9W	490	500

Soraa Brilliant 85 CRI*:

Model	CCT (K)	Beam (°)	Power (W)	Lumens (Im)	CBCP
SM16GA-09-25D-827-03	2700K	25°	9W	560	3090
SM16GA-09-36D-827-03	2700K	36°	9W	560	1460
SM16GA-09-60D-827-03	2700K	60°	9W	560	570
SM16GA-09-25D-830-03	3000K	25°	9W	590	3260
SM16GA-09-36D-830-03	3000K	36°	9W	590	1540
SM16GA-09-60D-830-03	3000K	60°	9W	590	600

^{*}This fixture is also compatible with Soraa`s 7.5W GU10 line of lamps. The 7.5W lamps are available in 10° beam spread. See Soraa`s full GU10 lamp offering at https://www.soraa.com/19-MR16-GU10#

Compatible Dimmers*:

Full lists of dimmer compatibility data are available at https://www.soraa.com/resources/compatibility

