

SECURITY AND ALARM CABLE

CL3R/CMR -Shielded Conductors
PVC Insulation & Jacket
300 Volt -16 AWG



CONSTRUCTION	
Conductor	- Stranded bare copper to ASTM B-3, B-8, and B-286
Insulation	- Color coded PVC
Shield	- 100% Overall aluminum/polyester - Stranded tinned copper drain wire
Jacket	- Gray PVC - Includes ripcord

COLOR CODE CHART	
Cond. #	Color
1	Black
2	Red
3	White
4	Green

Applications:

- Power limited control circuits
- Wiring of the following systems:
 - Intercom
 - Security
 - Audio
- Suggested Voltage Rating: 300 Volts.

Standards:

- NEC Article 725 Type CL3R
- NEC Article 800 Type CMR

Part #	AWG	Conductors	Insulation Thickness	Jacket Thickness	Nom. O.D.	Lbs./M'
DS11602	16	2	.010"	.015"	.189"	26.5
DS11603	16	3	.010"	.015"	.205"	38
DS21604	16	4	.010"	.015"	.220"	47.8

Note: The data shown is approximate and subject to standard industry and manufacturer tolerances.