

## Rigid Non-Metallic Conduit Bodies & Covers

### T&B Catalog Number:



**UPC Number:**  
**Status:**  
**Description:**

E986G  
03448120757  
Active

Type LB Conduit Body, Volume 32 Cubic Inches, Size 1-1/4 Inch, Length 6-13/32 Inches, Width 2-1/2 Inches, Material PVC, Color Gray, For use with Schedule 40 and 80 Conduit, Pack of 10

#### Features

Textured lids  
Foam-in-place gasket

#### Application

For use with Rigid Conduit

#### General

Trade Size (inches) 1-1/4  
Material Non-Metallic  
Volume (cu.in.) 32  
Conduit Body Shape LB

#### Dimension Information

C (inches) 1 3/32  
H (inches) 2 5/16  
L1 (inches) 7 31/32  
L2 (inches) 6 13/32  
L3 (inches) 6  
Q (inches) 2 1/2  
W (inches) 2 3/4

#### Packaging

Package in Units 10  
T&B Sold in UOM Each  
T&B Weight Per UOM 82.81 lbs. per 100

#### Application Support

T&B Sales Drawings wsd-ac05071  
Rigid Non-metallic Conduit Bodies Available on Website  
Specifications & Applications Available on Website

#### Certifications

RoHS Compliance Yes

#### Certifications



File Nbr:  
E11461

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com

