



75943-962: Three Light Ceiling Flush Mount



Collection: Windgate

Three Light Ceiling Flush Mount in Brushed Nickel Finish with Alabaster Glass

UPC #:785652020575

Finish: Brushed Nickel (962)

Dimensions:

Diameter:	15"	Wire:	6 1/2"
Height:	5 1/2"	Mounting Proc.:	Key Slots
Weight:	4.2 lbs.	Connection:	Mounted To Box

Bulbs:

- 3 - Medium A19 60w Max. 120v - Not included
- 3 - LED Medium A19 8w Max. 120v - Not included
- 3 - LED Medium A19 13.5w Max. 120v - Not included

Features:

- Easily converts to LED with optional replacement lamps
- Meets Title 24 energy efficiency standards
- Title 24 compliant if used with Joint Appendix (JA8) approved light bulbs listed in the California Energy Commission Appliance database.

Material List:

1 Body - Steel - Brushed Nickel

Safety Listing:

Safety Listed for Damp Locations
Safety Listed for Damp Locations

Instruction Sheets:

Bilingual (English - French) (HC-1700FB)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Shade	Glass	Alabaster	1				3 11/32	11 11/16	7/16			

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97308S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	3000	85
97408S	Frosted		A19	E-26 Medium	8	8	120v	50000	450	2700	85
97309S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	3000	85
97409S	Frosted		A19	E-26 Medium	13.5	13.5	120v	50000	800	2700	85

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	75943-962	1	785652020575	16	6	16	0.889	5.3	125	Yes
NJ Pallet		78		48	40	72	80	413.4		No
NV Pallet		78		48	40	72	80	413.4		No