



GE  
Lighting

68051 - F35/CW/C/U6/WM

F35/CW/C/U6/WM

Product Photo



#### GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	30 mg
Mercury-Picogram per mean lm hr	1530.6
Starting Temp (MIN) C-degrees	15 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	14000 h
Primary Application	Energy Saving
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T12

#### PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	1400 lm
Nominal Initial Lumen per Watt	47
Initial Lumens-nominal	1650 lm
Color Rendering Index-CRI	87
Color Temperature	4100 K

#### PRODUCT INFORMATION

Product Code	68051
Description	F35/CW/C/U6/WM
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168680516
Standard Package GTIN	10043168680513
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168680516

#### DIMENSIONS

Diameter	1.5 in
Nominal Length	22.5 in

#### ELECTRICAL CHARACTERISTICS

Rated power (Watts)	35 W
---------------------	------