

Kable Lite Insulated Cable



DESCRIPTION

Insulated cable is #10 gauge, tin-plated copper cable with kevlar core; sheathed in clear. Use insulated cable where required by local codes or in coastal areas, where salty air might corrode bare cables. Rated for 300 watts at 12 volts, 600 watts at 24 volts. Load: 300 watt maximum at 12 volts to 30' before voltage drop occurs; 600 watt maximum at 24 volts to 60' before voltage drop occurs.

OTHER INFORMATION

Cable is sold by the foot (0.3 m). Order the length of the Kable Lite run x 2 and add 10 percent to feed through turnbuckles.

WEIGHT

0.15lb / 0.07kg

ORDERING INFORMATION

700KLAINSCL LENGTH

12'



TECH LIGHTING®

7400 Linder Avenue
Skokie, Illinois 60077

T 847.410.4400
F 847.410.4500

www.techlighting.com

700KLAINSCL _____

FIXTURE TYPE: _____

JOB NAME: _____

NOTES: _____

