



Carlon®

ENT Flexible Raceway
T&B Catalog Number:

12008-750
 03448123201
 Active

UPC Number:
Status:
Description:

1 inch. Flex-Plus ENT non-metallic blue flexible raceway, 750 foot.

Features

- Recognized for use with PVC rigid non-metallic conduit fittings with all size of ENT.
- One piece ENT coupling, threaded terminator and rigid non-metallic conduit fittings are rated concrete tight without tape.
- Lightweight, hand bendable, and free from sharp edges which reduces installation time and saves money.

Application

- Flex-Plus Blue ENT is a non-metallic flexible raceway for use in walls, floors, and non-plenum ceilings.
- Residential, low or high rise, multi or single family. Commercial applications - low or high rise - office, retail, hotel/motel and restaurants.
- Other applications include schools, classrooms, dormitories, offices, fire alarm systems, solar photovoltaic systems, recreational vehicles and parks, and marinas and boatyards.

General

Pull Tape	Empty
Material	Non-Metallic
Color	Blue
Reel Length (feet)	750
Reel Type	Wood
Reel Size (Feet x Width)	36 x 24
Component Type	Flexible Raceway

Dimension Information

Size (inches)	1
Nominal Inside Diameter (inches)	1
Nominal Outside Diameter (inches)	1.315
Minimum Bend Radius (inches)	6

Packaging

T&B Order Multiple	750
Package in Units	750
T&B Sold in UOM	Feet
T&B Weight Per UOM	0.23 lbs. Each

Application Support

Product Specifications-Flex-Plus Blue ENT	Available on Website
Application Handbook-ENT	Available on Website

Certifications

RoHS Compliance Yes

Certifications



File Nbr:
E 73317

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com