



PRODUCT SEARCH



SUPP



DIST

[HOME](#)[WHAT'S NEW](#)[SERVICE / SUPPORT](#)[WHERE TO BUY](#)[INSTRUCTION MANUALS](#)[CONTACT](#)**Product Categories**[Hand Tools](#)[Holemaking](#)[Bending](#)[Fishing](#)[Cable Pulling](#)[Wire & Cable Termination](#)[Voice Data Video](#)[Testing & Measurement](#)[Storage & Material Handling](#)[Hydraulic Pumps &](#)[Miscellaneous](#)**Name:**

Wire Finder/Mini Locator

Cat #:

508S

UPC #:

08678

Spec:

Power Requirements (1) 9V each (transmitter and receiver, included)
 Battery Life Transmitter 35 hours nominal; Receiver 20 hours nominal
 Transmitter Frequency 447.5kHz Transmitter Power 9Vp-p (11mW)
 Voltage Protection 240VAC/500VDC Construction Transmitter/Receiver - high impact ABS plastic, Case - vacuum formed polyethylene
 Dimensions Transmitter - 4" x 2.3" x 1", Receiver - 6" x 2.35" x 1", Case - 9.5" x 8" x 3" Weight 2.6 lbs.

Description:

Used to trace energized or degenerated wires in walls and drop ceilings.

- Determines the approximate depth of a wire before digging begins.
- Transmitter and receiver are fully-adjustable for accurate locating.
- Reliable results on buried cables to depths of 3' and lengths up to 1000'.
- Quick-change test leads for use in any industry, even international power outlets.
- Voltage protection allows use on live AC circuits.
- Automatic shutoff prevents accidental battery discharge.
- Both the transmitter and receiver are fully-adjustable for accurate locating.

