



Powering Business Worldwide

[pe.eaton.com](http://pe.eaton.com)

## Quicklag Industrial Ground Fault Thermal-Magnetic Circuit Breaker

**QBHGF1020V**

**UPC:** 782116015825

**Dimensions:** x \* x \* x (L \* W \* H)

**Notes:** HACR rated

**Warranty:** 1 year

### Specifications:

- **Type:** Quicklag
- **Special Features:** 50° C Calibration, 5 mA Trip Sensitivity
- **Amperage Rating:** 20A
- **Interrupt Rating:** 22 kAIC
- **Number Of Poles:** Single-pole
- **Voltage Rating:** 120V
- **Mounting:** Bolt-on
- **Circuit Breaker Type:** QBHGF
- **Trip Type:** Non-Interchangeable

### Supporting documents:

- [Eatons Volume 4-Circuit Protection](#)
- [Circuit Breaker Time/Current Curves For QUICKLAG. Industrial Circuit Breakers](#)

**Certifications:** No Data

**Product compliance:** No Data

