



## Liquidtight Flexible Non-Metallic Conduit & Fittings

### T&B Catalog Number:

15007-001

### UPC Number:

03448123314

### Status:

Active

### Description:

3/4 Inch Gray Liquidtight Flexible Non-metallic Conduit, 1,000 Foot Reel

### Features

	Non-conductive and non-corrosive.
	Lightweight for easy handling, transportation and installation.
	Crush, abrasion and strain resistant.
	Provides superior wire protection
	Smooth interior ideal for pulling cable, no jagged edges.
	Maintains internal I.D. even in tight radius bends.
	Resistant to oil, acid, ozone, and alkaline.
	UL listed for outdoor use and sunlight resistant.
	UL listed for use as indicated in Article 356.2 of the NEC and Section 12-1300 of the Canadian Electrical Code, Part 1.
	Suitable for use at conduit temperatures of 80 degree C dry, 60 degree C wet and 60 degree C oil resistant as required by Section 15-6 of ANSI/NFPA 79 and UL 1660.
	Sequentially market footage

### Application

Control and Motor
Air conditioning and heating
Computer power distribution
Machine Tools
Console wiring
Transformer connections
Outdoor lighting

### General

Material	Non-Metallic
Color	Gray
Reel Length (feet)	1000

### Dimension Information

Size (inches)	3/4
Average O.D. (inches)	1.04
Average I.D. (inches)	0.825
Nominal Size (inches)	1/4

### Packaging

T&B Order Multiple	1000
Package in Units	1000
T&B Sold in UOM	Feet
T&B Weight Per UOM	0.21 lbs. Each

### Application Support

T&B Sales Drawings	wsd-ac04219
Product Overview-Carflex Liquidtight Flex-Available on Website	
ible Tubing	

## Notes

Available in black and gray.

Customer cut lengths available.

## Certifications

RoHS Compliance

Yes

## Certifications



File Nbr:

E95745

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)