



Representative Image

## Catalog No. THQL2120

Description: THQL 2 POLE 120/240V 10K IC 20 AMP

UPC No 783164012910

Products > Circuit Breakers > Residential Circuit Breakers > Feeder Plug-in Circuit Breakers

Q line circuit breakers are one-inch wide per pole, compact, thermal-magnetic devices designed for residential and commercial applications. The QL breakers are plug-in versions of the Q Line used for connection to load centers and lighting panels. All Q Line circuit breakers feature Quick-make / Quick-break mechanisms, common trip bars, and easy to spot trip indication to ensure safety and reliability. Q Line breakers are available in 1, 2, and 3 pole versions, can be ordered with auxiliary contact and shunt trip accessories, and can be ordered for use in HID applications.

### Descriptors

|             |                                 |
|-------------|---------------------------------|
| Category    | Feeder Plug-in Circuit Breakers |
| GO Schedule | R5                              |

### Specifications

|                                 |                      |
|---------------------------------|----------------------|
| Trip Style                      | Non-Interchangeable  |
| Frame Type                      | Q-Line               |
| Amperage                        | 20 A                 |
| System Voltage                  | 120 Vac, 120/240 Vac |
| Poles                           | 2                    |
| Trip Function                   | LI                   |
| Continuous Current Rated        | Standard             |
| 120 Vac Interrupting Rating     | 10 KAIC              |
| 120/240 Vac Interrupting Rating | 10 KAIC              |
| Suitable for Reverse Feed       | Yes                  |
| Product Line                    | Q-Line (Plug-In)     |
| Long Time                       | Fixed                |
| Instantaneous                   | Fixed                |
| Protective Relays               | No                   |
| Current Metering                | No                   |
| Special Markings                | HACR                 |
| GSA Compliance                  | Yes                  |

### Classifications

|           |        |
|-----------|--------|
| UL File # | E11592 |
|-----------|--------|

## Publications

| Title                                                                                                                                  | Publication No. | Publication Type                 |
|----------------------------------------------------------------------------------------------------------------------------------------|-----------------|----------------------------------|
| <a href="#">Q-Line Plug-In MCCB, 100A Frame 1-, 2-, or 3- Pole, Drawing</a><br>1-Page fully dimensioned outline drawing in .pdf format | 455C872-SH1     | Drawings-Outline and Dimensional |

**Additional Documentation:** Visit our [Publication Library](#) to find technical documentation, time current curves, CSI Specifications and promotional literature.