


BURNDY Catalog Number

YA32N

UPC Number

7818100189033

Description

400 CU 1-HOLE LONG 1/2

Status

Active

Web Use

BURNDY Product Line

Dimensional

Tongue Angle	Straight
Length (in)	4.09
Tongue Type	Standard
Barrell Style	Chamfered
Bolt Hole Size (in)	0.52
Barrel Type	Long
Thickness	0.19
B Length (in)	2.12
Pad Width (in)	1.40
Strip Length	2-3/16

General

Number of Holes	1
Product Description	Uninsul Cu Comp Terminal Code Cond, Bvl Entry, 1 Hole/W/O/InspWindow, 400 kcmil Code, 400 Navy, 600 V-35 kV, 1/2" Stud, Lng bbl, Blue, 19 or 470 index

Conductor(s)

Flex (Class G) Size - Range	N/A
Flex (Class H) Size - Range	N/A
Flex (Class I) Size - Range	N/A
Copper Solid Size (Range)	N/A
DLO Size (Range)	N/A
Copper Stranded (Range)	400 kcmil

Physical

Type of Plating	Tin - Electro Plated
Bolt Hole Size	1/2
Color Code	Blue
Plated (Yes or No)	Y
Index Number	19,470
Product Material	Copper

Approvals / Certifications

UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N

Documentation
For further technical assistance, please contact us
BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175