



GE
Lighting

66854 - F35/CX41/U3/WM-CIRCLEVILLE C AND I SKUS IN PULP T

F35/CX41/U3/WM

Product Photo



GENERAL CHARACTERISTICS

Base Description	Medium Bi-Pin
Base Type	Pin/Plug-In
Mercury Content	30 mg
Mercury-Picogram per mean lm hr	980.7
Starting Temp (MIN) C-degrees	15 °C
Bulb Material	Sodalime glass
Rated Life Hours-nominal	14000 h
Primary Application	Energy Saving
Product Technology	Linear Fluorescent
Base	G13
Bulb Shape	T12

PHOTOMETRIC CHARACTERISTICS

Mean Lumens nominal	2185 lm
Nominal Initial Lumen per Watt	74
Initial Lumens-nominal	2300 lm
Color Rendering Index-CRI	87
Color Temperature	4100 K

PRODUCT INFORMATION

Product Code	66854
Description	F35/CX41/U3/WM
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168668545
Standard Package GTIN	10043168668542
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168668545

DIMENSIONS

Diameter	1.5 in
Nominal Length	23.0 in

ELECTRICAL CHARACTERISTICS

Rated power (Watts)	35 W
---------------------	------